



EIBENSTOCK
Elektrowerkzeuge



PATENTED

Innovative drive solution

One motor – two contra rotating tools
for optimal mixing results



TwinMix 1800 T

**The mobile station for thorough mixing
with a wide range of application**

The mobile stations for thorough mixing up to 50 kg

USE:

Homogenous and lump free mixing of numerous materials with different viscosity

Especially convenient for the mixing of self-levelling floor levelling compounds, plaster, thin-bed mortar, fillers

Building construction and civil engineering, landscaping, floor renovators, tilers



OPTIMAL MIXING RESULTS:

Mixing paddle with scraper and fast running inner rod – avoids material deposits on the bucket rim

Two electronic speed levels – start mixing function with reduced speed

Soft start, constant speed, high torque



Tipper with 4 wheels, 2 steerable (accessory)
– especially designed for clean and precise pouring of self-levelling filler and levelling compounds



Transport carriage with 2 big wheels (supplied)
– flexible and mobile at the job site



Timer for setting the requested mixing time for special requirements of the material manufacturer (accessory)

Specifications	TwinMix 1800 T (prepared for timer function)
Power input	1800 W
Rated voltage	230 V ~
Rated speed mixing rod	250/450 rpm
Rated speed mixing paddle	20/36 rpm
Bucket size	65 l
Spindle connection	M 14/Special
Weight	70.0 kg
Order no.	07623000
Supplied on a pallet incl. mixing rod, mixing paddle, bucket 65 l and transport carriage	

Versatile application possibilities – best mixing results



masonry mortar



thin-bed mortar



plaster



floating screed



tile cement



two-component materials



insulation board adhesive



screed



filler

Fast, uninterrupted work when using several mixing carriages, f. e. for levelling filler



saves at least **50%** time

- ☞ saves time and costs
- ☞ reduces the risk that the material is setting too fast in wet-on-wet cycle

10:15



Mixture 1



Mixture 2

10:20



Mixture 2




Mixture 3

Reduction of hazardous dusts



Connection for dust exhaust Ø 35 mm as well as funnel tube with brushes – dust reduced filling and mixing of the materials

- ☞ dust reduced construction site
- ☞ cleanliness in the interior



Accessories	Order no.
Timer for TwinMix 1800 T	32352000
Mixing paddle	31451000
Scraper for mixing paddle (3 pieces)	32351000
Universal stirring rod	31452000
Transport carriage	09Z11000
Tipper	09Z12000
Bucket 65l	32341000

Ihr Fachhändler: